

## APPLICATIONS

- Aerospace analysis
- Amusement ride testing
- Automotive safety
- Biomechanics
- Blast testing
- Helicopter & aircraft
- Impact testing
- Motorsports incident recorder
- Parachute deployment
- Transportation monitoring: truck, air, ship & rail
- Ride & handling
- Sports & safety equipment

# TSR PRO & TSR PRO-HB

## Data Loggers with Internal Triaxial Accelerometer



The ultra-small TSR PRO and TSR PRO-HB are portable data loggers with built-in triaxial accelerometers. Ideal for both short duration tests and long term monitoring, the TSR time and date stamps each event and stores up to 2,000 events in flash memory.

The TSR PRO & TSR PRO-HB are self-powered data loggers with three internal accelerometers ideal for unattended monitoring of acceleration and vibration. An advanced sleep mode helps save battery power and the module **“wakes” for an event**, which can be triggered by acceleration threshold, contact closure switch input or voltage input. After each event, data writes to non-volatile flash memory, then the unit automatically re-arms and is ready to capture the next event. Both the TSR PRO & TSR PRO-HB are available with a USB-rechargeable battery or a user-replaceable AA battery.

The interface connector makes it easy to access trigger inputs/outputs, USB and an external power input option.




## Features

- Compact and rugged, the data logger easily mounts on or can be embedded inside a test article
- Stores up to 2,000 events or 34 hours of continuous recording @ 1K sps; data writes directly to flash memory
- Battery options: Built-in rechargeable (via USB) or user-replaceable AA battery
- Sensor range options from  $\pm 20$  g to  $\pm 500$  g
- Variable sampling rates from 1,000 to 20,000 sps/channel
- Logs temperature, date and time for each event
- IP67 rated for dust protection and immersion in water
- Complies with ISO 6487 and SAE J211 recommended practices, as well as NHTSA and FAA requirements
- Intuitive software for arming, downloading and viewing data; simple data files can be viewed in Excel

## Software

TSR Control software provides easy-to-use tools for test setup and viewing events. With a focus on speed and simplicity, TSR Control lets users configure the recorder, view real-time sensor output and review time-history data.



## PRODUCTS

Diversified Technical Systems designs and manufactures data acquisition systems and sensors for experienced test professionals.

## SERVICES

24/7 Worldwide Tech Support  
ISO 17025 (A2LA) Calibration  
On-site Calibration & Training  
Application Consulting  
Software Integration  
OEM/Embedded Applications

## WORLDWIDE SUPPORT

HELP CENTER (24/7/365 Access)  
DTS Technical Centers  
Global Sales Partners

## HEADQUARTERS

Seal Beach, California USA

## CONTACT US

Phone: +1 562 493 0158  
Email: sales@dtsweb.com  
Web: www.dtsweb.com

## Specifications



| MODEL                  | TSR PRO   | TSR PRO-HB  |
|------------------------|---|---|
| Internal Accelerometer | MEMS Triaxial (DC response)                             | MEMS Triaxial (DC response)                               |
| Sensor Range Options   | ±20, ±50 or ±250 g                                      | ±500 g  |
| Frequency Response     | DC to 300 Hz<br>4-pole Butterworth<br>SAE/ISO Class 180 | DC to 1650 Hz<br>4-pole Butterworth<br>SAE/ISO Class 1000 |
| Sampling Rate          | 1,000 to 20,000 samples/sec/channel<br>16-bit ADC       | 5,000 to 20,000 samples/sec/channel<br>16-bit ADC         |
| Battery Options        | Lithium Rechargeable -or- Non-Rechargeable              | Lithium Rechargeable -or- Non-Rechargeable                |

| POWER / Battery Life Estimate*  | ACTIVE MODE   | MOTION / MAGNET MODE  |
|---|---|---|
| BATTERY TYPE  | System always armed, collects 512 pre-trigger data points | Internal low-g motion sensor, detects motion and arms within 1 second |
| Lithium Rechargeable (900 mAh)  | 24 hrs**  | Up to 3 months***   |
| Lithium Non-Rechargeable (2400 mAh)   | 72 hrs**  | Up to 6 months***   |
| External Battery (via 15-pin D-Sub connector)   | Depends on customer battery size                          | Depends on customer battery size                                      |
| <p>*NOTE: Battery life will vary based on type, application, duty-cycle and sampling rate. Contact a DTS sales engineer to determine the best product and estimated battery life for your specific application.<br/>** Estimate based on potential low temperature operation and/or older battery (actual may be longer).<br/>*** Depends on XML settings for motion sensor timeout and actual duty-cycle of motion.</p> <p>See TSR Battery Life article available on DTS Help Center</p> |   |   |

| PHYSICAL                                 |  |
|--|--|
| Size:                                    | 72 x 72 x 22 mm (2.83 x 2.83 x 0.87")  |
| Mass:                                    | 237 g (8.37 oz)  |
| Enclosure Material:                      | Anodized Aluminum  |
| ENVIRONMENTAL                            |  |
| Operating Temperature:                   | -20 to 60°C (Rechargeable)<br>-20 to 85°C (Non-Rechargeable)   |
| Humidity:                                | 95% RH non-condensing  |
| Shock:                                   | 500 g operating; 2000 g survivable   |
| IP Rating:                               | IP67   |
| MEASUREMENT CHANNEL OVERVIEW             |  |
| Sensors:                                 | Three MEMS DC response accelerometers  |
| Filters:                                 | 4-pole Butterworth   |
| Data Conversion:                         | 16-bit ADC, one per channel  |
| Sampling Rate:                           | 1,000 to 20,000 samples per sec. per channel   |
| Pre-Trigger Data:                        | 512 samples available  |
| Memory:                                  | 1 GB direct-write flash  |
| POWER SAVING FEATURES (Software Enabled) |  |
| Motion Sense:                            | Detects slight movement to bring unit from deep sleep to ready mode.   |
| Magnet Detect:                           | Hall-effect sensor can be used to bring unit in/out of deep sleep when magnet is present   |
| Max Battery Life:                        | Depends on application, duty cycle and use of power saving features. Operational life can be greatly extended by using external power. |

| TRIGGERING  |  |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
|---|--|----------------------------------|--------------------------|----------------------------------|----|----|--------------|----|----|--------------|-----|-----|-----------|-----|-----|------------|
| Software Trigger:   | Level triggering on each axis  |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
|   | <table border="1"> <thead> <tr> <th>TSR g Range ±</th> <th>Approx. Actual g Range ±</th> <th>Programmable Level Trigger Range</th> </tr> </thead> <tbody> <tr> <td>20</td> <td>35</td> <td>±0.7 &lt;&gt; ±3.5</td> </tr> <tr> <td>50</td> <td>70</td> <td>±1.4 &lt;&gt; ±7.0</td> </tr> <tr> <td>250</td> <td>350</td> <td>±7 &lt;&gt; ±35</td> </tr> <tr> <td>500</td> <td>700</td> <td>±14 &lt;&gt; ±70</td> </tr> </tbody> </table> | TSR g Range ±                    | Approx. Actual g Range ± | Programmable Level Trigger Range | 20 | 35 | ±0.7 <> ±3.5 | 50 | 70 | ±1.4 <> ±7.0 | 250 | 350 | ±7 <> ±35 | 500 | 700 | ±14 <> ±70 |
| TSR g Range ±   | Approx. Actual g Range ±   | Programmable Level Trigger Range |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| 20  | 35   | ±0.7 <> ±3.5                     |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| 50  | 70   | ±1.4 <> ±7.0                     |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| 250   | 350  | ±7 <> ±35                        |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| 500   | 700  | ±14 <> ±70                       |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| Hardware Trigger:   | Contact closure or isolated voltage input<br>Voltage or contact-closure output   |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| Status:   | Voltage or contact-closure output  |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| POWER   |  |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| External:   | 6-36 VDC   |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| Battery Options:  | USB-rechargeable lithium polymer -or- Non-rechargeable lithium primary   |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| CALIBRATION   |  |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| Calibration Supplied:   | NIST traceable   |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| ISO 17025:  | ISO 17025 (A2LA Accredited) available  |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| Service Options:  | Factory, On-site & Service Contracts available   |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| SOFTWARE  |  |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| Product Name:   | TSR Control  |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| Data Management:  | Date/Time/Temp recorded for each event   |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| Post-Processing:  | SAE Filters, View multiple channels/tests, Head Injury Criteria (HIC)  |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| Operating Systems:  | Windows® 7/8/10 (32- and 64-bit)   |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| Communication:  | USB  |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |
| Additional DTS data logger models are available with a variety of sensor options, shock ratings, sampling rates and more. |  |                                  |                          |                                  |    |    |              |    |    |              |     |     |           |     |     |            |



Does your application require different sensors ranges or higher shock ratings? Ask about the TSR 6DXP and TSR 6DXC



Specifications subject to change without notice.  
© Diversified Technical Systems, Inc.